


Pickup Truck Solutions



Pickup Truck Products

*Simple to Operate.
Rugged Durability.
Complete Solutions.*

Curb-Sider® (VSL-6000)

The exterior version of the world's most popular vehicle lift gives you unsurpassed versatility for loading and unloading mobility devices at the rear of the truck bed!

The *Curb-Sider* allows you to avoid the tailgate by lifting from the curb-side. With 400 lb/181 kg of lifting capacity, the *Curb-Sider* can handle nearly any scooter or power wheelchair with ease.

- Standard tough texture coating, along with an exterior pendant package protects your *Curb-Sider* from the elements
- The fold-down lift head means added driver visibility and increased available cargo space when the lift is not in use
- Direct Gear Drive Technology (no chains to slip or loosen) means virtually maintenance-free operation



Turny™ (TAS 2570/2570E)

A marvelous Turning Automotive Seating™ (TAS™) product that rotates out of the cab and lowers to the desired height!

With the *Turny* you can easily operate both the *Pow'r Topper* and the *Out-Rider* lift (see following pages) to load and unload a wheelchair, scooter or power wheelchair from outside the cab, then smoothly power the seat up and into your pickup.


- Seat lowers to transfer height for mobility device users
- Driver and passenger side applications available



Stow-Away™ (TAS-1850)

A fully powered, compact transfer seat for pickups and large SUVs that is mounted outside the vehicle!

- Original factory seats retain all their manual and powered functions, No obstructions in the cab or seating compartment
- A sealed container, normally affixed to running board mounts holds the *Stow-Away*
- By simply pushing a single button, a drawer opens and the seat rises to the designed transfer height, then up to the vehicle seat height.





Out-Sider[®] Meridian[™] (ASL-250)

***Transport your scooter or power wheelchair
outside your pickup truck!***

Lightweight, yet tough as nails, The *Out-Sider Meridian* will allow you to take your mobility device wherever you go, quickly and easily!

- Easy, one button operation
- Texture coated platform for increased traction & durability
- Drive on/off either side of platform
- Optional *Swing-Away[™]* allows easy access to tailgate



Bruno also offers the *Turny*, a rotating/lowering seat to assist individuals who have difficulty transferring in and out of higher vehicles. (shown above)



**Shown with optional
footrest**

Out-Rider[®] (PUL-1100)

***Lift and store your wheelchair, scooter or
power wheelchair in the bed of your pickup truck
while sitting up front!***

The *Out-Rider* is fully automatic and easy to operate, with a hand-held pendant. It can lift a folding/rigid wheelchair, scooter or power wheelchair weighing up to 350 lb/159 kg!

- Stows your mobility device in the bed of your truck
- Conveniently delivers your mobility device next to the front seat
- Designed to withstand the rigors of outdoor use
- Driver and passenger side applications available

Pow'r Topper™ (PCL-1900)

**Lift and lower your truck bed cap
at the touch of a button!**

The *Pow'r Topper* installs into select full-size pickup trucks. Operate this power cap lift from the comfort of the cab with a hand-held pendant.

- Protects your mobility device, Bruno lift and cargo under the cap
- When combined with the *Out-Rider* and *Turny* or *Stow-Away*, the *Pow'r Topper* provides a "total pickup truck mobility solution"



Cab-Sider™ (PUL-1700)

**Protect your wheelchair from the weather
with this handy interior lift!**

Compact and simple, the *Cab-Sider* lets your truck bed carry the heavy loads while your wheelchair is safe and dry in the cab. Just roll the wheelchair next to the vehicle, transfer, connect the docking device and use the hand-held pendant to do the rest.



- Store your folding manual wheelchair behind the front seat of your extended cab truck
- When combined with the *Turny* or *Stow-Away* you have a "total mobility solution"

Innovation... for your Independence & Convenience.

KEY SPECIFICATIONS	ASL-250	PUL-1100	PUL-1700	PCL-1900	TAS-1850	TAS-2570/ TAS-2570E	VSL-6000
Maximum Weight Capacity	350 lb/ 159 kg	350 lb/ 159 kg	90 lb/ 41 kg	N/A	300 lb/ 136 kg	330 lb/ 150 kg	400 lb/ 181 kg
Fully Powered	yes	yes	yes	yes	yes	yes	yes
3 Year Warranty	yes	yes	yes	yes	yes	yes	yes
Hand-Held Pendant Controls	yes	yes	yes	yes	yes	yes	yes
Powered by Vehicle Battery	yes	yes	yes	yes	yes	yes	yes
Requires Structural Modification to Vehicle	no	no	no	no	no	no	no
Can Reinstall in Another Vehicle	yes	yes	yes	yes	yes	yes	yes
Eligible for Auto Manufacturer Rebate	yes	yes	yes	yes	yes	yes	yes

IMPORTANT: Contact your authorized Bruno dealer for specific details on your vehicle!

Represented by:

BRUNO INDEPENDENT LIVING AIDS, INC.®

1780 Executive Drive, P.O. Box 84, Oconomowoc, WI 53066

www.bruno.com

